



What is the pressure capability of the ARE brand all PEEK column coupler - FAQ

These ARE-Applied Research brand HPLC column couplers are actually unions (*cat# 47450-01, 47450-02, 47450-03, or 47450-04*) and are standard HPLC items that if installed properly while using standard temperatures and normal HPLC solvents, they should be able to withstand pressures up to 6,000 psi.

Click [HERE](#) for column coupler ordering information and pictures.

ARE-APPLIED RESEARCH™

Printed from the Chrom Resource Center
Copyright 2025, All Rights Apply
MicroSolv Technology Corporation
9158 Industrial Blvd. NE, Leland, NC 28451

Tel: (732) 380-8900
Fax: (910) 769-9435
Email: customers@mtc-usa.com
Website: www.mtc-usa.com