


## Slurry Reservoir Kit

For 4.6 mm ID columns 100 mm long and shorter



1. Slurry Reservoir, Black PEEK 7.5mm ID, 100 mm long
2. PEEK sealing rings / frit spacers
3. *Nothing shown for this kit*
4. End fitting to connect tubing from a pump to reservoir
5. Packing adapter to connect the reservoir to the column

### MicroSolv Technology Corporation

9158 Industrial Blvd. NE, Leland, NC 28451

tel. (732) 380-8900, fax (910) 769-9435

Email: [info@mtc-usa.com](mailto:info@mtc-usa.com)

Website: [www.mtc-usa.com](http://www.mtc-usa.com)