


Slurry Reservoir Kit

For 4.6 mm ID columns longer than 100 mm



1. Slurry Reservoir, Black PEEK 7.5mm ID, 100 mm long
2. PEEK sealing rings / frit spacers
3. *Nothing shown for this kit*
4. End fitting to connect tubing from a pump to reservoir
5. Packing adapter to connect the reservoir to the column

MicroSolv Technology Corporation

9158 Industrial Blvd. NE, Leland, NC 28451

tel. (732) 380-8900, fax (910) 769-9435

Email: info@mtc-usa.com

Website: www.mtc-usa.com