


Slurry Reservoir Kit

For 7.5 mm ID columns 100 mm and shorter



1. Slurry Reservoir, Black PEEK 7.5 mm ID, 300 mm long
2. PEEK sealing ring / frit spacer for the bottom and top connection
4. End fitting to connect tubing from a pump to reservoir
5. Packing adapter to connect the reservoir to the column

MicroSolv Technology Corporation

9158 Industrial Blvd. NE, Leland, NC 28451

tel. (732) 380-8900, fax (910) 769-9435

Email: info@mtc-usa.com

Website: www.mtc-usa.com